

P. 1 -1041 <コロコンローラ SPEC >

文言追加

型式		(L)		¥基準単価								
Type	ホイール 個数	P=30	P=35	一般ナット						Uナットタイプ		
				CRONF CRON	CROC	CROS	CROJ	CROJS	CRONFB	CRONFU CRONU	CROCU	CROSU
	2	(58)	(68)	990	2,010	1,680	1,510	1,760	1,460	1,090	2,110	1,780
	3	(88)	(103)	1,150	2,770	2,310	2,090	2,300	1,620	1,300	2,920	2,460
	4	(118)	(138)	1,410	3,520	2,940	2,660	2,900	1,880	1,610	3,720	3,140
	5	(148)	(173)	1,670	4,290	3,580	3,210	3,460	2,140	1,920	4,540	3,830
	6	(178)	(208)	1,910	5,050	4,210	3,780	4,030	2,380	2,210	5,350	4,510
	7	(208)	(243)	2,160	5,830	4,860	4,340	4,600	2,630	2,510	6,180	5,210
	8	(238)	(278)	2,410	6,580	5,490	4,890	5,160	2,880	2,810	6,980	5,890
	9	(268)	(313)	2,670	7,340	6,120	5,460	5,730	3,140	3,120	7,790	6,570
	10	(298)	(348)	2,910	8,120	6,770	6,010	6,300	3,380	3,410	8,620	7,270
	11	(328)	(383)	3,170	8,880	7,400	6,590	6,860	3,640	3,720	9,430	7,950
	12	(358)	(418)	3,420	9,630	8,030	7,140	7,430	3,890	4,020	10,230	8,630
	13	(388)	(453)	3,670	10,400	8,670	7,710	8,000	4,140	4,320	11,050	9,320
	14	(418)	(488)	3,920	11,160	9,300	8,260	8,560	4,390	4,620	11,860	10,000
	15	(448)	(523)	4,170	11,910	9,930	8,820	9,130	4,640	4,920	12,660	10,680
	16	(478)	(558)	4,430	12,690	10,580	9,390	9,700	4,900	5,230	13,490	11,380
	17	(508)	(593)	4,680	13,450	11,210	9,950	10,260	5,150	5,530	14,300	12,060
	18	(538)	(628)	4,920	14,200	11,840	10,510	10,830	5,390	5,820	15,100	12,740
	19	(568)	(663)	5,180	14,970	12,480	11,070	11,400	5,650	6,130	15,920	13,430
	20	(598)	(698)	5,430	15,730	13,110	11,640	11,900	5,900	6,430	16,730	14,110
	21	(628)	(733)	5,690	16,480	13,740	12,200	12,500	6,160	6,740	17,530	14,790
	22	(658)	(768)	5,920	17,250	14,380	12,750	13,100	6,390	7,020	18,350	15,480
	23	(688)	(803)	6,180	18,010	15,010	13,320	13,600	6,650	7,330	19,160	16,160
	24	(718)	(838)	6,440	18,790	15,660	13,880	14,200	6,910	7,640	19,990	16,860
	25	(748)	(873)	6,690	19,540	16,290	14,450	14,800	7,160	7,940	20,790	17,540
	26	(778)	(908)	6,930	20,300	16,920	15,000	15,300	7,400	8,230	21,600	18,220
	27	(808)	(943)	7,180	21,080	17,570	15,570	15,900	7,650	8,530	22,430	18,920
	28	(838)	(978)	7,440	21,840	18,200	16,130	16,500	7,910	8,840	23,240	19,600
	29	(868)	(1013)	7,630	22,590	18,830	16,680	17,060	8,100	9,080	24,040	20,280
	30	(898)	(1048)	7,940	23,360	19,470	17,250	17,600	8,410	9,440	24,860	20,970
	31	(928)	(1083)	8,190	24,120	20,100	17,800	18,200	8,660	9,740	25,670	21,650
	32	(958)	(1118)	8,440	24,870	20,730	18,380	18,700	8,910	10,040	26,470	22,330
	33	(988)	(1153)	8,690	25,650	21,380	18,930	19,300	9,160	10,340	27,300	23,030

Ⓢ 荷重量は、切削ローラはホイール1個あたり30kgf(294N)、樹脂ローラはホイール1個あたり20kgf(196N)となります。

<訂正用>

Ⓢ 荷重量は、切削ローラはホイール1個あたり30kgf(294N)、樹脂ローラはホイール1個あたり20kgf(196N)となります。