

P. 1 -937 <図表>

文言削除

■シール付

型式		D	a	B	B <sub>1</sub>	e	f	基本動定格荷重 C (kN)	基本静定格荷重 C <sub>0</sub> (kN)	トラック負荷容量 (kN)		限界回転数 (rpm)	質量 (g)	¥基準単価				
Type	d									NASTZ	NASTFZ			NASTZS	NASTFZS	NASTZC	NASTFZC	
(クラウンタイプ) (フラットタイプ) NASTZ NASTFZ NASTZS NASTFZS NASTZC NASTFZC	6	19	14	13.8	14	2.5	0.8	4.12	4.55	1.37	3.53	8000	24.5	1,500	4,350	1,430	4,150	5,200
	8	24	17.5					5.68	5.89	1.86	4.51	6800	39	1,600	4,810	1,510	4,380	5,400
	10	30	23.5	15.8	16			9.70	9.67	2.45	6.86	6000	65	1,670	4,840	1,580	4,580	5,700
	12	32	25.5					10.4	10.9	2.74	7.35	5200	75	2,010	5,830	1,830	5,310	6,400
	15	35	29.0					12.3	14.3	—	8.04	4000	83	—	—	1,990	—	—
	17	40	32.5	19.8	20			17.4	20.9	—	11.8	3800	135	—	—	2,080	—	—
	20	47	38.0					19.2	24.5	—	13.8	3400	195	—	—	2,330	—	—

kgf=N×0.101972

<訂正用>

型式	
Type	
(クラウンタイプ)	(フラットタイプ)
NASTZ	NASTFZ
NASTZS	NASTFZS
	NASTFZC