

P643 (規格表)

フランジ付タイプ Ds寸法を一部修正

■フランジ付タイプ

kgf=N×0.101972

Catalog No.		d	D	B	D ₁	C	r (mm)	基本定格荷重				取付関係寸法		質量 (g) (参考)	¥単価	
スチールタイプ	ステンレスタイプ							Cr (動) N		Cor (静) N		Ds (mm)	R (mm)		1～9コ	
								スチール	ステンレス	スチール	ステンレス				スチールタイプ	ステンレスタイプ
FL682ZZ	SFL682ZZ	2	5	2.3	6.1	0.6	0.08	169	143	50	40	2.7	0.08	0.24	410	430
FL692ZZ	SFL692ZZ		6	3.0	7.5	0.8	0.15	330	281	99	79	3.0	0.15	0.45		
FL682AZZ	SFL682AZZ	2.5	6	2.6	7.1	0.8	0.08	209	178	74	59	3.7	0.08	0.42	440	450
FL692AZZ	SFL692AZZ		7	3.5	8.5	0.9	0.15	386	328	129	103	3.85	0.15	0.68		
FL673ZZ	SFL673ZZ	3	6	2.5	7.2	0.6	0.08	242	178	94	59	3.6	0.08	0.26	460	500
FL683ZZ	SFL683ZZ		7	3	8.1	0.8	0.1	390	331	130	104	3.9	0.1	0.53		
FL693ZZ	SFL693ZZ		8	4	9.5	0.9	0.15	560	474	180	144	4.2	0.15	0.72		
FL623ZZ	SFL623ZZ		10		11.5	1	0.15	640	536	224	175			1.8		
FL674ZZ	SFL674ZZ	4	7	2.5	8.2	0.6	0.08	222	217	88	86	4.6	0.08	0.35		
FL684ZZ	SFL684ZZ		9	4	10.3	1	0.15	640	544	224	179	5.0	0.1	1.14		
FL694ZZ	SFL694ZZ		11		12.5			715	545	276	182	5.2	0.15	2		
FL624ZZ	SFL624ZZ		13	5	15		0.2	1310	1106	490	390	5.6	0.2	3.5		
FL675ZZ	SFL675ZZ	5	8	2.5	9.2	0.6	0.08	217	185	91	72	6.2	0.15	0.4	410	500
FL685ZZ	SFL685ZZ		11	5	12.5	1	0.15	715	607	282	225			2.18		
FL695ZZ	SFL695ZZ		13	4	15		0.2	1080	915	430	346	6.6	0.2	2.7		
FL605ZZ	SFL605ZZ		14	5	16			1330	1130	505	406			3.9		
FL676ZZ	SFL676ZZ	6	10	3	11.2	0.6	0.1	465	422	196	174	7.0	0.15	0.74	460	470
FL686ZZ	SFL686ZZ		13	5	15	1.1	0.15	1080	918	440	352			3.04	440	
FL696ZZ	SFL696ZZ		15		17	1.2	0.2	1350	1139	530	418	7.6	0.2	4.3	410	500
FL606ZZ	SFL606ZZ		17	6	19		0.3	2190	1924	865	677	8	0.3	6.5		
FL678ZZ	SFL678ZZ	8	12	3.5	13.6	0.8	0.1	515	462	252	219	8.8	0.1	0.86	460	580
FL688ZZ	SFL688ZZ		16	5	18	1.1	0.2	1610	1368	715	572	9.6	0.2	4.47		
FL698ZZ	SFL698ZZ		19	6	22	1.5	0.3	1990	1901	865	734	10	0.3	8.4		
FL608ZZ	SFL608ZZ		22	7	25			3350	2799	1400	1103			13		
FL6700ZZ	SFL6700ZZ	10	15	4	16.5	0.8	0.15	855	684	435	348	10.3	0.15	2.1	780	1,050
FL6900ZZ	SFL6900ZZ		22	6	25	1.5	0.3	2695	2156	1273	1018	13.2	0.3	11.1	680	940

<訂正用>

10.3
13.2