

# P1610 (注釈)

赤枠内の注釈を削除



Order  
注文例



Price  
価格

■数量スライド価格 (◎1円未満切り捨て) P.81

数量	1~4	5~9	10~19	20~29	◎表示数量超えは お見積り
値引率	価格表	5%	10%	15%	

~~形状加工価格には  
数量スライド価格は  
適用されません。~~

●ネジ部

Catalog No.

L - M - E - A

Type 形状 D

JPFJ R 12 - 40 - 6

JPFMC T 12 - 35 - 5 - E8 - A15



Delivery  
出荷日

3 日目発送

<価格計算例>

JPFJR12-40-M6の場合  
1,330 + 370 = 1,700

D	L最短~59			L60~100			形状加工価格 (本体+)			
	JPFJ	JPFM	JPFMC	JPFJ	JPFM	JPFMC	F形状	R形状	Q形状	T形状
6	830	1,000	910	—	—	—	120	370	500	370
8	1,000	1,160	1,080	—	—	—	120	370	500	370
10	1,160	1,330	1,250	—	—	—	120	370	500	370
12	1,330	1,500	1,410	1,500	1,660	1,580	120	370	500	370
15	1,500	1,660	1,580	1,660	1,830	1,750	180	500	620	500
16	1,660	1,830	1,750	1,830	2,000	1,910	180	500	620	500
18	1,830	2,160	2,000	2,080	2,410	2,250	180	500	620	500
20	2,160	2,500	2,330	2,410	2,750	2,580	250	620	750	620
30	2,500	2,830	2,660	2,830	3,160	3,000	250	620	750	620
40	2,830	3,160	3,000	3,160	3,500	3,330	250	620	750	620

M	M×Pitch
3	M3×0.5
4	M4×0.7
5	M5×0.8
6	M6×1.0
8S	M8×1.0
8	M8×1.25
10S	M10×1.25
10	M10×1.5
12S	M12×1.25
12	M12×1.5
14S	M14×1.5
18S	M18×1.5

<訂正用>

