

D2・3のp6公差訂正

■スタンダード

型式			D寸公差		P 選択	L	B	C	E	ℓ
Type	形状記号	D	m6	p6						
JPRB GJPRB SJPRB CJPRB (バフ研磨品) MJPRB MGJPRB MCJPRB ◎D≥5に適用	B (m6) PB (p6)	2	+0.008	+0.012	3 4	4	3	0.5	3	0
		3	+0.002	+0.006	4 5 6	5	5			
		4			5 6		6	1	4	
		5	+0.012	+0.020	6 8	10				
		6	+0.004	+0.012	8 10		8			
		8	+0.015	+0.024	10 12 13			1.5	5	
		10	+0.006	+0.015	12 13 15	15				
		12			13 15 16		10	2	6	
		13	+0.018	+0.029	15 16	22				
		16	+0.007	+0.018	20 25			3	7	2
		20	+0.021 +0.008	+0.035 +0.022	25 30	30	15			

 <訂正用>

+0.012
+0.006