

先端止めねじタイプのD寸・25のL寸訂正

■先端止めねじタイプ

型式				L	P	B	d	F	M ₁	W	ℓ	A	M ₂	N
Type	形状記号	材質記号	D	指定0.01mm単位	選択	指定0.5mm単位			(並目)				(並目)	(並目)
SPF (先端止めねじ)	A ^(おねじ) B ^(内ねじ)	B SU	12	20.00 (30.00) ~80.00	6	4.0~6.0	8	4	M8	10	10	10	M5	M3
			15	20.00 (40.00) ~80.00	8	5.0~10.0	10	5	M10	13	10	15	M8	M4
			20	25.00 (45.00) ~80.00	10 12	5.0~15.0	12	5	M12	17	10	20	M8	M4
			25	30.00 (50.00) ~80.00	12 16	5.0~19.0	16	5	M16	20	12	24	M10	M4
			30	35.00 (65.00) ~80.00	16 20	5.0~23.0	20	6	M20	24	18	28	M16	M4

①L寸()は内ねじに適用

<訂正用>

L
指定0.01mm単位
20.00 (30.00) ~80.00
20.00 (40.00) ~80.00
25.00 (45.00) ~80.00
30.00 (50.00) ~80.00
35.00 (65.00) ~80.00