


RoHS





Type		M材質	S表面処理
クラウン	槽溝付ストレート		
RBWAC	RBWAM	A5056	—
RBWWC	RBWWM	A6063(クラウンタイプのD38以上)	白アルマイト

6.3 / ( 1.6 / )



■キー溝形状



■新JIS (B1301) キー溝寸法表

呼び	dH9	bJS9	t公差
N8	8	3	±0.0125
N10	10	3	±0.0125
NK10	10	4	1.8 +0.1
N12	12	5	±0.0150
N15	15	6	2.3
N20	20	6	2.8
N25	25	8	±0.0180
N30	30	10	3.3 +0.2
N35	35	12	0
N40	40	12	±0.0215
N50	50	14	3.8

<訂正用>

■新JIS (B1301) キー溝寸法表

呼び	dH9	bJS9	t公差
N8	8	3	±0.0125
N10	10	3	±0.0125
NK10	10	4	1.8 +0.1
N12	12	5	±0.0150
N15	15	6	2.3
N20	20	6	2.8
N25	25	8	±0.0180
N30	30	10	3.3 +0.2
N35	35	12	0
N40	40	12	±0.0215
N50	50	14	3.8