

赤枠内 数値を一部変更


■外ねじ式ストリップボルト
—軸径公差 h7—

RoHS



HDSMSB
(ステンレス)

識別用
刻印(h)



☑材質 SUSXM7

※強度区分 A2-50

M×ピッチ

M×ピッチ	Dh7	A	B	C	E	T	L+F加工条件
3×0.5							
4×0.7	4.5	7	2.5	1.6	3	4.5	L+F≦46
5×0.8	5.5	9			3.5	5.5	L+F≦47
6×1.0	6.5	10	3	2	4	6.5	L+F≦59
8×1.25	8	13	5	3	6	8.7	L+F≦70
10×1.5	10	16	6	4	8	10.8	L+F≦72

<訂正用>

Dh7	A	B	C	E	T	L+F加工条件
4.5	7	2.5	1.6	3	4.5	L+F≦46
5.5	9			3.5	5.5	L+F≦47
6.5	10	3	2	4	6.5	L+F≦59
8	13	5	3	6	8.7	L+F≦70
10	16	6	4	8	10.8	L+F≦72